



YSM31L78, Uninsulated Parallel Splice For 350 kcmil

By Burndy
Catalog # [YSM31L78](#)

Uninsulated Parallel Splice For 350 kcmil

Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

Splicing

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Str	350 kcmil
Compact Size	
Conductor - Copper Str	350 kcmil
Compact Size Range	
Conductor Size	350 KCMIL
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size	350 kcmil
Range	
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Dimension - B Length inch	0.68 in
Dimension - Outside Diameter inch	0.88 in
Length	0.821 in
Dimension - Inside Diameter inch	0.68 in
Dimension - Length Overall inch	0.82 in

General

Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 12 Digit	781810375716
UPC 14 Digit GTIN	00781810375716
Material	Copper
Plating Type	Tin
UPC	781810375716

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	29600

Product Assets

[Catalog \[English\]](#)