



YSV14BBOX, Uninsulated Splice For 16 - 14 AWG

By Burndy
Catalog # [YSV14BBOX](#)

Uninsulated Splice, 16-14 AWG, Rolled Splice, Electrolytic Copper, Electro-Tin Plated

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For All Heavy Duty Industrial And General Purpose Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	16-14 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size
Conductor - Copper Str Size	16-14 AWG

Configuration

Connector Type	Rolled Butt Splice
----------------	--------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.64 in
Dimension - Strip Length inch	1/4

General

Feature - Barrel Style	Chamfered
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYLINK™
Sub Brand	HYLINK
Product Type	Splice
UPC	781810525531
Type	Splice
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810525531

Logistics

Minimum Pack Quantity	100
Pallet Quantity	1
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)