



YSM40L144, Uninsulated Parallel Splice For 800 kcmil

By Burndy
Catalog # [YSM40L144](#)

Uninsulated Parallel Splice For 800 kcmil



Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

Splicing

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Str	800 kcmil
Compact Size	
Conductor - Copper Str	800 kcmil
Compact Size Range	
Conductor Size	800 KCMIL
Conductor - Copper Str Size	800 kcmil
Conductor - Copper Str Size	800 kcmil
Range	
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Outside Diameter inch	1.35 in
Length	1.477 in
Dimension - Inside Diameter inch	1.03 in
Dimension - Length Overall inch	1.48 in

General

Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 12 Digit	781810371145
UPC 14 Digit GTIN	00781810371145
Material	Copper
Plating Type	Tin
UPC	781810371145

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	7400

Product Assets

[Catalog \[English\]](#)