



YSM4C, Uninsulated Parallel Splice For 26,813 - 42,613 cmils

By Burndy
Catalog # [YSM4C](#)



Uninsulated Parallel Splice For 26,813 - 42,613 cmils, Seamless Tubing, Beveled Barrel, Tin Plated

Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	26,813 - 42,613 cmils
Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Length Overall inch	0.50 in
Dimension - Strip Length inch	9/16

General

Feature - Barrel Style	Chamfered
Plated	Yes
Color Code	Gray
Product Family	COMPRESSION
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	8
Product Type	Splice
UPC	781810805770
Type	YSM
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810805770
UPC 14 Digit GTIN	00781810805770

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)