



YSV18BBOX, Uninsulated Splice For 22 - 18 AWG

By Burndy
Catalog # [YSV18BBOX](#)

Uninsulated Splice For 22 - 18 AWG

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For All Heavy Duty Industrial And General Purpose Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	22-18 AWG
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	22-18 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

- CU C Str Aircraft-Size

Configuration

Connector Type	Rolled Butt Splice
----------------	--------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Dimension - L Length Overall mm	16 mm
Dimension - Strip Length inch	1/4
Dimension - Length Overall inch	0.62 inch

General

Sub Brand	HYLINK
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 14 Digit GTIN	00781810525548
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810525548

Logistics

Minimum Pack Quantity	100
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)