




YSP28T, Compression Splice, 4/0 AWG Cu, Tapered End

By Burndy
Catalog # [YSP28T](#)

4/0 AWG, CU, Taper End SPLICE



Features

- Copper seamless barrel designed with tapered ends per EEL Standard TD160, for use on voltages 5kV through 35kV, this aids in preventing corona emission and simplifies taping for lower installation cost
- Barrel also features internal chamfer at wire entry to ensure smooth insertion of wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements

Application

Wire Splice

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	4/0 AWG
Conductor - Material	COPPER
Wire Size	#4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	62 mm
Dimension - B Length inch	1.16 in
Dimension - Length Overall inch	2.45 in
Dimension - Strip Length inch	1-3/16 in

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Purple
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	15
UPC	781810001301
Type	YSP-T, High Voltage, Long Barrel
Material	Copper
Plating Type	Electro Tin plated
Finish Type	Tin-Plated

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)