



YSV4CLNK, Uninsulated Splice For 4 AWG (Nickel Plated)

By Burndy
Catalog # [YSV4CLNK](#)

Uninsulated Splice For 4 AWG (Nickel Plated)

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion
- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	AN 4
Conductor Size	4 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Outside Diameter inch	0.38 in
Dimension - L Length Overall mm	28 mm
Dimension - Inside Diameter inch	0.28 in
Dimension - Strip Length inch	5/8
Dimension - Length Overall inch	1.12 in

General

Die Index	40
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 12 Digit	781810050095
UPC 14 Digit GTIN	00781810050095
Material	Copper
Plating Type	Nickel
UPC	781810050095

Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	99000

Product Assets

[Catalog \[English\]](#)