


Z2MLDN630B, Stud Mole Assembly

By Burndy
Catalog # [Z2MLDN630B](#)

STUD MOLE ASSY



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Configuration

Number Of Outlets	6
Connector Type	Mole

Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - Width inch	3.5 in
Dimension - B Length inch	3.25 in
Dimension - Width fraction	3-1/2 in
Dimension - Length Overall inch	16 in

General

Plated	Y
Insulation Type	Diatex
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810056615
Insulation	Y
Material	Mixed
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810056615
UPC 14 Digit GTIN	00781810056615

Logistics

Minimum Pack Quantity	1
Pallet Quantity	75
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)