



YSR34FX26FXLTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 2/0 Flex, includes clear heat shrink

By Burndy
Catalog # YSR34FX26FXLTCKITC

CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel B 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-2/0 AWG
Conductor - Copper Flex K Size B Range	2/0 AWG
Conductor - Copper Flex K Tap	2/0 AWG
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Flex M Size A Range	350 kcmil
Conductor - Copper Flex M Size B Range	2/0 AWG
Conductor - Copper Flex M Run	350 KCMIL



Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Str Size	350 KCMIL-2/0 AWG
Conductor - Copper Flex I Tap	2/0 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex I Size B Range	2/0 AWG
Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper Flex G Size A Range	350 kcmil
Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex H Run	350 KCMIL
Conductor Size	350 KCMIL-2/0 AWG
Conductor - Copper Str Size B	2/0 AWG
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex G Size B Range	2/0 AWG
Conductor - Copper Flex G Tap	2/0 AWG
Conductor - Copper Flex M Tap	2/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	2/0 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B Range	2/0 AWG
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size A Range	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000	Feature - Barrel Type	Standard
		Feature - Barrel Style	Skived
Dimensions		Plated	Y
Package Height	0.000 in	Color Code	Blue, Black
Package Weight	0.000 lb.	UPC	781810434383
Package Length	0.000 in	Color Code - Side B	Black
Package Width	0.000 in	Color Code - Side A	Blue
Dimension - L Length Overall	100 mm	Material	Copper
mm		Plating Type	Tin - Electro Plated
Dimension - Strip Length inch	1.60 in	Finish Type	Tin-Plated
Dimension - B Length fraction	1-11/16 in	UPC 12 Digit	781810434383
Dimension - B Length inch	1.69 in	UPC 14 Digit GTIN	00781810434383
Dimension - Length BB inch	1.13 in		
Dimension - Length Overall	3.94 in		
inch			
		Logistics	
General		Minimum Pack Quantity	1
Trade Name	HYREDUCER™	Pallet Quantity	1728
Die Index	19/13	Carton Quantity	12
Die Index - Element A	• 19 • L80	Operational	
Die Index - Element B	13	Temperature Rating	194
Die Index Run Side	• 19 • L80	Product Assets	
Die Index Tap Side	13	Catalog [English]	
		Installation Manual [French, English]	

