



Z34NR, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z34NR](#)

Socket And Nut Assembly, 500 kcmil, 5/8-18, 3-11/16 in L, Tin-Plated



Features

- Socket and Nut Assembly designed for use with Burndy MOLE

Application

Designed for use with Burndy mole

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	17/32 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Weight	1.2 lb.
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	3.69

Force Related

Installation Torque Recommended	450 lb-in in-lb
---------------------------------	-----------------

General

Plated	Yes
Product Family	Utility Overhead & Underground Distribution>Network Underground>Accessories
Sub Brand	MOLE
Product Type	Mechanical
UPC	781810821220
Type	Z-NR
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810821220
UPC 14 Digit GTIN	00781810821220

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2784
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)