



YSR34FX6CFXLTKITC, Compression
Splice Reducer, Barrel A 350 kcmil, Barrel B
#6 Flex, includes clear heat shrink

By Burndy
Catalog # YSR34FX6CFXLTKITC

CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel
B 6 Flex G,H,I,K,M,DLO, 6 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-6 AWG
Conductor - Copper Flex K Size	6 AWG
B Range	
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex K Size	350 kcmil
A	
Conductor - Copper Flex K Size	6 AWG
B	
Conductor - Copper Flex K Size	350 kcmil
A Range	
Conductor - Copper Flex M Size	6 AWG
B	
Conductor - Copper Flex M Size	350 kcmil
A Range	
Conductor - Copper Flex M Size	6 AWG
B Range	
Conductor - Copper Flex M Run	350 KCMIL

Conductor - Copper Flex M Size	350 kcmil
A	
Conductor - Copper Str Size	350 KCMIL-6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex I Size	6 AWG
B	
Conductor - Copper Flex I Size	6 AWG
B Range	
Conductor - Copper Flex G Size	350 kcmil
A	
Conductor - Copper Flex G Size	350 kcmil
A Range	
Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex H Run	350 KCMIL
Conductor Size	350 KCMIL-6 AWG
Conductor - Copper Str Size B	6 AWG
Conductor - Copper Flex H Size	350 kcmil
A	
Conductor - Copper Flex G Size	6 AWG
B Range	
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	6 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex H Size	350 kcmil
A Range	
Conductor - Copper Flex H Size	6 AWG
B Range	
Conductor - Copper Flex I Size	350 kcmil
A	
Conductor - Copper Flex I Size	350 kcmil
A Range	

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	108 mm
Dimension - Strip Length inch	1.60 in
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	4.26 in

General

Trade Name	HYREDUCER™
Die Index	19/7
Die Index - Element A	• 19 • L80
Die Index - Element B	7
Die Index Run Side	• 19 • L80
Die Index Tap Side	7
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived

Plated	Y
Color Code	Blue, Gray
UPC	781810473887
Color Code - Side B	Blue
Color Code - Side A	Blue
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810473887
UPC 14 Digit GTIN	00781810473887

Logistics

Minimum Pack Quantity	10
Pallet Quantity	900
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand