

Eaton 170M1368

Catalog Number: 170M1368

Eaton Bussmann series high speed square body fuse, 125 A, 690 V (IEC), 700 V (UL), , Size 0, Top fuse status indicator



General specifications

Product Name	Catalog Number
Eaton Bussmann series high speed square body fuse	170M1368
	EAN
	5027590440851
UPC	Product Length/Depth
051712216692	105 mm
Product Height	Product Width
46 mm	300 mm
Product Weight	Compliances
135.7 g	CE Marked
	RoHS Compliant
Certifications	
UL Recognized	
IEC Rated	

Product specifications

Type

Fuse

Application

Semiconductor, DC Common bus, DC drives, power converters/rectifiers

Amperage Rating

125 A

Breaking capacity

200 kA

Fuse indicator

Top fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Utilization category

aR (accompanied semiconductor protection)

Voltage type

AC

Fuse size

000

Rated voltage AC

690 V

Current type

AC

Class

Class aR

Clearing (I₂T)

8500 at 660 V

Watt losses

28 W

Fuse shape

Square body, slotted offset bolted tags

Pre arc (I₂T)

1200

Color

None

Resources

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

[UKCA 170M size 000 10A to 315A](#)

[CE 170M size 000 10A to 315A](#)

Interrupt rating

200 kAIC

Connection

Blade end x blade end

Construction size

Other

Voltage rating

690 V (IEC), 700 V (UL)

Fuse type

DIN 43653

/80 Visual indicator



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)