

Eaton CH141DNU

Catalog Number: CH141DNU

Eaton's Bussmann series 1-Pole + 1 Neutral modular fuse holder, rated at 690 V a.c./750 V d.c. (IEC), 700 V a.c. (UL), 50 Amps (IEC and UL), suitable for 14 x 51 mm Cylindrical fuses



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage cylindrical fuse holder	CH141DNU
	Model Code
	1P+N 14x51 Fuse Holder
UPC	EAN
051712685122	5027590496643
Product Length/Depth	Product Height
76 mm	92 mm
Product Width	Product Weight
53 mm	192.667 g
Compliances	Certifications
CE Marked	IEC 60269-2
RoHS Compliant	EAC
	IEC 60269-1
	UL Listed File E14853

Product specifications

Used with

C14G, C14M, FW-A14F fuses

Type

Fuse holder

Application

Industrial and Commercial applications

Amperage Rating

50 A

Number of Poles

Single-pole + N

Width in number of modular spacings

3

Built-in depth

51.5 mm

Fuse size

14 x 51 mm

Operating temperature details

-20°C to +70°C

Voltage rating at AC

690 V a.c. (IEC) and 700 V a.c. (UL)

Voltage rating at DC

750 V d.c. (IEC)

Fuse type

C14G

C14M

Lockable

Yes

Accessories

JV-L Multipole connector kit, CH14-CTP IP20 Protection accessory

Torque rating

Max 3.5 Nm

Concurrently switching N-neutral

No

Material

Polyester

Resources

Catalogs

CA134002EN

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

UKCA Modular fuse-holders

CE Modular fuse-holders

Multimedia

Eaton Bussmann – Modular fuse holders

Technical data sheets

10080 14 x 51 mm Modular fuse holder

720147 10 x 38 mm Modular fuse holder

10115 22 x 58 mm Modular fuse holder

Optical defect indication

No

Mounting method

DIN rail

2 x M4 Panel mounting screws

Degree of protection

IP20

Voltage rating

690 V

Model

CH14



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)