

**Intelligent Control**

An integrated, electronic digital thermostat allows you to stay in control of your temperature at all times and reduces up to 30% on your heating bill

**Ultra Quiet Operation**

Auto adjusting, variable speed fan delivers the quietest most comfortable, consistent temperature

**Mistake Proof Install**

With the built-in smart sensor you can easily update old heaters and not worry about damaging your new heater, or whether you have 120, 208 or 240 Volts



Product Dimensions (WxHxD)  
9" x 12" x 4"  
22.9 cm x 30.5 cm x 10.2 cm



**Complete Unit (includes wall can, white grille and built-in electronic thermostat)**

Model	Watts	Volts	Amps	BTU	Weight (lbs./kg)
CEC163TW	1000 / 1600 / 1500	120 / 240 / 208	8.3 / 6.7 / 7.2	3415 / 5460 / 5120	8.1 / 3.6

**Heater Assembly (requires wall can and grille)**

Model	Watts	Volts	Amps	BTU	Weight (lbs./kg)
CE163T	1000 / 1600 / 1500	120 / 240 / 208	8.3 / 6.7 / 7.2	3415 / 5460 / 5120	4.4 / 2.0

**Accessories (sold separately)**

Model	Description
CC	Galvanized wall can, single
CC10	Galvanized wall can, 10-pack
CCSMW	Surface mount wall can, white
CCSMB	Surface mount wall can, black
CEGW	Grille kit, white
CEGB	Grille kit, black
CAMW	Adapter plate, 18-1/2" W x 22" H, white
SAMW	Adapter plate, 12" W x 21-1/4" H, white