

Gantry Cranes

Model K90-4 - 4 Ton Capacity

**QUICKSHIP
PROGRAM**

SPECIFICATIONS		Nominal Span (ft.)						
		Clamp Connection			Bolt Connection			
4 Ton Capacity*		10	12	14	16	20	24	
Maximum Height Under Beam (ft.)	7	Model Number	K90-4-7/10	K90-4-7/12	K90-4-7/14	K90-4-7/16	K90-4-7/20	K90-4-7/24
		Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"
		Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"
		Weight (lbs.)	975	1125	1200	1450	1625	2125
		Minimum Height	5'-0"					
		Support Width (C)	4'-0"					
	9	Model Number	K90-4-9/10	K90-4-9/12	K90-4-9/14	K90-4-9/16	K90-4-9/20	K90-4-9/24
		Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"
		Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"
		Weight (lbs.)	1125	1250	1325	1575	1750	2250
		Minimum Height	6'-0"					
		Support Width (C)	5'-0"					
	10	Model Number	K90-4-10/10	K90-4-10/12	K90-4-10/14	K90-4-10/16	K90-4-10/20	K90-4-10/24
		Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"
		Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"
		Weight (lbs.)	1175	1300	1375	1625	1800	2300
		Minimum Height	7'-0"					
		Support Width (C)	5'-6"					
12	Model Number	K90-4-12/10	K90-4-12/12	K90-4-12/14	K90-4-12/16	K90-4-12/20	K90-4-12/24	
	Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"	
	Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"	
	Weight (lbs.)	1325	1450	1525	1775	1975	2450	
	Minimum Height	8'-0"						
	Support Width (C)	6'-6"						
14	Model Number	K90-4-14/10	K90-4-14/12	K90-4-14/14	K90-4-14/16	K90-4-14/20	K90-4-14/24	
	Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"	
	Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"	
	Weight (lbs.)	1425	1550	1625	1875	2075	2550	
	Minimum Height	9'-0"						
	Support Width (C)	7'-6"						
16	Model Number	K90-4-16/10	K90-4-16/12	K90-4-16/14	K90-4-16/16	K90-4-16/20	K90-4-16/24	
	Inside Span (A)	9'-5"	11'-5"	13'-5"	15'-5"	19'-5"	23'-5"	
	Overall Length (B)	11'-6"	13'-6"	15'-6"	17'-6"	21'-3"	25'-3"	
	Weight (lbs.)	1500	1625	1700	1975	2150	2625	
	Minimum Height	10'-0"						
	Support Width (C)	7'-6"						
Beam Height (in.)		10	12		15		18	
Flange Width (in.)		4.7	5		5.5		6	
Caster Diameter (in.)		8						

* Total weight of hoist and trolley not to exceed 20% of rated capacity.



The Caldwell Group • 800-628-4263 • www.caldwellinc.com

Krane-King® Section
2014-2016 Master Catalog