



YSV28LBOX, Uninsulated Splice For 4/0 AWG

By Burndy
Catalog # [YSV28LBOX](#)

Uninsulated Splice For 4/0 AWG

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

UNINSULATED BUTT SPLICE

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Str Aircraft Size	AN 0000
Conductor Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type Seamless Butt Splice

Current

Voltage - Maximum 600 V

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	7/8 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.88 in
Dimension - Outside Diameter inch	0.77 in
Dimension - L Length Overall mm	49 mm
Package Height	0.000 in
Dimension - Strip Length inch	7/8 in
Dimension - Length Overall inch	1.94 in

General

Sub Brand	SPLICE, HYLINK
Die Index	46
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 14 Digit GTIN	00781810324714
Material	Copper
Plating Type	Tin
UPC	781810324714

Logistics

Minimum Pack Quantity	1
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)