



# Industrial LED Lighting



## Compact Alpha Series

Designed for use in different work environments:

A compact construction combining state-of-the-art LED technology with a sturdy, anodized aluminum casing highly resistant to liquids and machine tool debris.

Suitable in any workplace where the space is very limited, but at the same time requires high-performance and intense lighting.



## TRACKALPHA Series

Designed for universal use:

Lighting system for industrial, automation, medium and large CNC applications. Lamp with sturdy anodized aluminum structure resistant to shavings, vibrations, front diffusing tempered glass 0.20" (5mm) thick.

Suitable in any workplace where there are liquids and oils.



## Herionova Recessed Series

Used in large CNC machines or when brighter illumination in wet industrial environments is required.

Also suitable for industrial applications such as automation processes and medium CNC machines. State-of-the-art Light Emitting Diode (LED) technology inside a robust, anodized aluminum casing, resistant to vibrations and machining debris, front tempered frosted glass 0.16 in (4 mm) thick.

Particularly suitable in workplaces where oils and other liquids are in use.





## Herionova Cable Series

Used for application in diverse working environments.

Suitable for industrial applications, automation processes, medium and large CNC machines. State-of-the-art Light Emitting Diode (LED) technology inside a robust, anodized aluminum casing, resistant to vibrations and machining debris, front tempered frosted glass 0.16 in (4 mm) thick.

Particularly suitable in workplaces where oils and other liquids are in use.

## Accessories





# LED Light Bars - TRACKALPHA Series

## Features

- Structure made entirely of anodized aluminum
- Outer diameter 2.76 in (70mm) to be integrated into most workspaces
- 5 lengths from 12.6 in (321mm) to 50.43 in (1281mm)
- Protection rating IP67
- Operating temperature -20 to +45°C [-4 to +113°F]
- Diffused light beam 120°
- LED lifespan: (L 70) > 60,000 hours
- Light color 5,000 K - CRI 80
- Power supply 24VDC
- 9.8 ft (3m) power cord
- Attaching with included TAFX03 side-mounting brackets



**TA0221S0403**

LED Light Bars - TRACKALPHA Series								
Part Number	Price	Light Color	Operating Voltage	Power Consumption (Watts)	Body Material	Light Length (in [mm])	Cable Length ft [m]	Drawing Link
<a href="#"><u>TA0221S0403</u></a>	\$164.00	Daylight white	24VDC	13	Anodized aluminum	12.6 [321]	9.8 [3]	<a href="#"><u>PDF</u></a>
<a href="#"><u>TA0321S0403</u></a>	\$188.00			19.5		17.36 [441]		<a href="#"><u>PDF</u></a>
<a href="#"><u>TA0521S0403</u></a>	\$258.00			32.5		26.81 [681]		<a href="#"><u>PDF</u></a>
<a href="#"><u>TA0721S0403</u></a>	\$335.00			45.5		36.25 [921]		<a href="#"><u>PDF</u></a>
<a href="#"><u>TA1021S0403</u></a>	\$465.00			65		50.43 [1,281]		<a href="#"><u>PDF</u></a>

Mounting bracket included with each light bar

Replacement Bracket - TRACKALPHA Series			
Part Number	Price	Description	Drawing Link
<a href="#"><u>TAFX03</u></a>	\$27.00	CCEA side bracket, replacement, stainless steel. For use with CCEA TRACKALPHA series LED light bars.	<a href="#"><u>PDF</u></a>



**TAFX03**



# LED Light Bars - TRACKALPHA Series Specifications

## Specifications

LED Light Bars - TRACKALPHA Series Technical Specifications					
Part Number	TA0221S0403	TA0321S0403	TA0521S0403	TA0721S0403	TA1021S0403
Luminous Color	Daylight white				
Color Temperature	5000K				
Luminous Flux (lm)	1,300	1,950	3,250	4,550	6,500
Rated Voltage	24VDC				
Operating Voltage Range	22-28 VDC				
Rated Current Consumption	0.54 A @ 24VDC	0.81 A @ 24VDC	1.35 A @ 24VDC	1.90 A @ 24VDC	2.71 A @ 24VDC
Rated Power Consumption (W)	13	19.5	32.5	45.5	65
Operating Ambient Temperature	-20 to +45°C [-4 to +113°F]				
Operating Ambient Humidity	Less than 90% (no condensation)				
Mounting Location	Indoors				
Mounting Direction	All directions				
Protection Rating	IP67				
Insulation Resistance	More than 5MΩ at 500VDC between the terminals and the chassis				
Withstanding Voltage	500VAC applied for 1 minute between terminals and chassis without breaking insulation				
Vibration Resistance	19.6 m/s <sup>2</sup> (30Hz, back and forth: 2h, right to left: 2h, up and down: 2h)				
Weight (lb [kg])	2.65 [1.20]	3.64 [1.65]	5.62 [2.55]	7.28 [3.30]	10.25 [4.65]
Agency Approvals *	cURus in compliance with UL2108 CE				

\* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.