

HEAVY DUTY AT SERIES

CHECKERS HEAVY DUTY AT SERIES WHEEL CHOCKS are made with durable, lightweight polyurethane. Featuring replaceable aluminum base plates with posi-grip cleats or anti-slip rubber traction pads, the AT Series is ideal for underground mining equipment, fire fighting vehicles and large utility vehicles.

MEETS NFPA & SAE SPECIFICATIONS NFPA 1901, 1906 & 1911 standard requires two or more wheel chocks to be mounted on fire apparatuses in readily accessible locations before being placed into service.

SAE-J348 standard presents design, manufacturer, and testing criteria for wheel chocks.

- Lighter weight with tough urethane construction
- ANSI compliant color written guidelines on proper chocking procedures
- Complies with SAE-J348, NFPA 1901, 1906, and 1911 Standard
- Resistant to oils, fuels and solvents
- Recessed carrying handle on the backside of the chock
- Replaceable aluminum traction cleats or rubber pads
- Mounting hole for ropes, chains or brackets

AT3514 recommended tire diameter 36 in. to 46 in. (91.4 cm to 116.8 cm)

AT3514 Series Wheel Chocks comply with NFPA 1901, 1906, 1911, and meet SAE-J348 standard

- For vehicles with tire sizes of 36 in. to 46 in. (91.4 cm to 116.8 cm) and gross vehicle operating weight up to 150,000 lb. (68,039 kg)



(See Mounting Brackets below)

Model	Base Design	Length	Width	Height	Weight	Prop 65
AT3514-AC-Y	Aluminum Cleat Cored Bottom	21 in. (53.3 cm)	11.25 in. (28.6 cm)	12.25 in. (31.1 cm)	16.5 lb. (7.5 kg)	⚠
AT3514-FBAC-Y	Aluminum Cleat Flat Bottom	21 in. (53.3 cm)	11.25 in. (28.6 cm)	12.25 in. (31.1 cm)	18.8 lb. (8.6 kg)	⚠
AT3514-RP-Y	Rubber Pad Cored Bottom	21 in. (53.3 cm)	11.25 in. (28.6 cm)	12.25 in. (31.1 cm)	16.1 lb. (7.3 kg)	⚠
AT3514-FBRP-Y	Rubber Pad Flat Bottom	21 in. (53.3 cm)	11.25 in. (28.6 cm)	12.25 in. (31.1 cm)	17.5 lb. (8.0 kg)	⚠
ATCLEAT-3514	Replacement Aluminum Cleat for cored or flat bottom				2.0 lb (.9 kg)	-
ATPAD-2514	Replacement Rubber Pad for cored or flat bottom				.9 lb (.4 kg)	-

⚠ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov. See pg 80-82

AT3512 recommended tire diameter 28 in. to 38 in. (71.1 cm to 96.5 cm)

AT3512 Series Wheel Chocks comply with NFPA 1901, 1906, 1911, and meet SAE-J348 standard

- For vehicles with tire diameter of 28 in. to 38 in. (71.1 cm to 96.5 cm) and gross vehicle operating weight up to 80,000 lb. (36,287 kg)




(See Mounting Brackets below)

Model	Base Design	Length	Width	Height	Weight	Prop 65
AT3512-AC-Y	Aluminum Cleat Cored Bottom	15.5 in. (39.4 cm)	8.5 in. (21.6 cm)	8.25 in. (21.0 cm)	7.1 lb. (3.2 kg)	⚠
AT3512-FBAC-Y	Aluminum Cleat Flat Bottom	15.5 in. (39.4 cm)	8.5 in. (21.6 cm)	8.25 in. (21.0 cm)	7.5 lb.(3.4 kg)	⚠
AT3512-RP-Y	Rubber Pad Cored Bottom	15.5 in. (39.4 cm)	8.5 in. (21.6 cm)	8.25 in. (21.0 cm)	7.1 lb. (3.2 kg)	⚠
AT3512-FBRP-Y	Rubber Pad Flat Bottom	15.5 in. (39.4 cm)	8.5 in. (21.6 cm)	8.25 in. (21.0 cm)	7.5 lb. (3.4 kg)	⚠
ATCLEAT-3512	Replacement Aluminum Cleat for cored or flat bottom				.625 lb (.3 kg)	-
ATPAD-2512	Replacement Traction Pad for cored or flat bottom				2.0 lb (.9 kg)	-

⚠ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov. See pg 80-82

AT SERIES MOUNTING BRACKET for AT3512, AT514 & AT3500 Chocks

Model	Description	Coating	Weight	Prop 65
AT2512VM	Vertical Mounting Bracket for 3512 Series 14" x 12" x 5.75"	Zinc Plated	3.2 lb. (1.5 kg)	-
AT2512HM	Horizontal Mounting Bracket for 3512 Series 16" x 11.13" x 6.25"	Zinc Plated	5.3 lb. (2.4 kg)	-
AT2514HM	Horizontal Mounting Bracket for 3514 Series 21.75" x 14.13" x 6.75"	Zinc Plated	8.0 lb. (3.7 kg)	-
AT2500	Universal Dual Mounting Bracket holds 2 each 3500 Series Wheel Chocks of any size. 26.26" (66.7 cm) Length Bracket Rod with 6" (15.2 cm) Square Mounting Plate.	Black Powder Coated Finish	13.5 lb. (6.2 kg)	-



* Ton is the U.S. standard, equivalent to 2,000 lb. (907 kg)