

## <0.7 hp (500 W) Die Grinders

# The CP3030 Series Benefits

### LIGHTWEIGHT & ERGONOMIC

- Industrial die grinder
- Industrial grade durability up to 1,000 hours between maintenance intervals
- Operator comfort

## CP3030-420R ★★

20,000 RPM



#### FEATURES

- Streamlined safety lever
- Rear Exhaust
- Gearless durable construction

### CP3030-418R/424R

Same features as CP3030-420R with respectively 18,000 - 24,000 rpm

### CP3030-420F/424F

Same features as CP3030-420R with same speeds and Front exhaust.

NOT FOR CE MARKET

## CP3030-520R ★★

20,000 RPM



#### FEATURES

- Streamlined safety lever
- Rear Exhaust
- Gearless durable construction

### CP3030-518R

Same features as CP3030-520R with 18,000 rpm



See accessories on pages 92-97

## CP3030-325R ★★

25,000 RPM



### FEATURES

- Streamlined safety lever
- Rear Exhaust
- Gearless durable construction



## CP3030-325R

### CP3030-330R

Same features as CP3030-325R with 30,000 rpm

### CP3030-325F/330F

Same features as CP3030-325R with 25,000, 30,000 rpm and Front exhaust.

NOT FOR CE MARKET

★ GENERAL MAINTENANCE   ★★ INDUSTRIAL MAINTENANCE & PRODUCTION   ★★★ SUPER INDUSTRIAL

MODEL	PART NUMBER	FREE SPEED			POWER		COLLET CAPACITY		AIR CONS. @LOAD		NET WEIGHT		LENGTH		VIBRATION LEVEL ISO 28927 (m/s <sup>2</sup> )		SOUND PRESS.	SOUND POWER	AIR INLET
		rpm	hp	W	in.	mm	cfm	l/s	lb	kg	in.	mm	a	k	ISO 15744 - dB(A)	in.			
CP3030-325F	615 160 4120	25,000	0.4	300	1/4	6.35	16.3	7.7	1.1	0.5	6.1	154	<2.5	-	85	96	1/4		
CP3030-325R	615 160 4090	25,000	0.4	300	1/4	6.35	17	8	1.1	0.5	6.1	154	<2.5	-	80	91	1/4		
CP3030-330F	615 160 4110	30,000	0.4	300	1/4	6.35	17.6	8.3	1.1	0.5	6.1	154	<2.5	-	84	95	1/4		
CP3030-330R	615 160 4100	30,000	0.4	300	1/4	6.35	19.1	9	1.1	0.5	6.1	154	<2.5	-	77	88	1/4		
CP3030-418R	615 160 4130	18,000	0.54	400	1/4	6.35	21.2	10	1.8	0.8	6.8	174	<2.5	-	75	86	1/4		
CP3030-420F	615 160 4170	20,000	0.54	400	1/4	6.35	21.4	10.1	1.8	0.8	6.8	174	<2.5	-	82	93	1/4		
CP3030-420R	615 160 4140	20,000	0.54	400	1/4	6.35	23.3	11	1.8	0.8	6.8	174	<2.5	-	76	87	1/4		
CP3030-424F	615 160 4180	24,000	0.54	400	1/4	6.35	23.1	10.9	1.8	0.8	6.8	174	<2.5	-	82	93	1/4		
CP3030-424R	615 160 4150	24,000	0.54	400	1/4	6.35	23.3	11	1.8	0.8	6.8	174	<2.5	-	78	89	1/4		
CP3030-518R	615 160 4190	18,000	0.7	500	1/4	6.35	27.6	13	1.9	0.9	6.8	174	<2.5	-	80	91	1/4		
CP3030-520R	615 160 4200	20,000	0.7	500	1/4	6.35	29.7	14	1.9	0.9	6.8	174	<2.5	-	80	91	1/4		

All models: Hose int. 3/8" (9.5 mm) - @90 PSI (@6.3 Bar)

Listed specifications are for reference only. Please check documents in each tool.