



YSV6CLBR, Uninsulated Splice For 6 AWG

By Burndy
Catalog # [YSV6CLBR](#)

Uninsulated Splice For 6 AWG

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Aircraft Size	AN 6
Conductor Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.50 in
Dimension - Outside Diameter inch	0.31 in
Dimension - L Length Overall mm	28 mm
Package Height	0.000 in
Dimension - Strip Length inch	5/8 in
Dimension - Length Overall inch	1.12 in

General

Die Index	39
Trade Name	HYLINK™
Plated	N
Feature - Barrel Style	Chamfered
Type	Splice
UPC 14 Digit GTIN	00781810273029
Material	Copper
Plating Type	Unplated
UPC	781810273029

Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)