



Z2MLDN820, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [Z2MLDN820](#)



Cu Alloy MOLE Stud Connector, 2000 Amps Capacity, 8 Outlets, 600 kcmil, 1-1/2" Stud Dia., Diatex Insulation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	600 kcmil
Range	
Conductor - Copper Str Size	600 kcmil

Configuration

Number Of Outlets	8
Connector Type	Mole

Dimensions

Dimension - Height inch	3.1
Dimension - B Length fraction	2-11/16 in
Dimension - Width inch	4.94
Diameter - Stud	1.5 in
Dimension - B Length inch	2.69 in
Dimension - Threads per inch	12

Dimension - Length Overall inch	16.94
---------------------------------	-------

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	Y
Insulation Type	Diatex
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810017289
Insulation	Y
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017289
UPC 14 Digit GTIN	00781810017289

Logistics

Minimum Pack Quantity	1
Pallet Quantity	96
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)