



Pipe clamps

B1508 thru B1564S Conduit/Strut Clamps


- Safety Factor of 3
- Clamps without saddles are not recommended for flexible conduit or cable
- All Sizes Include:
1/4"-20 slotted hex head machine screw
- Standard finish: ZN



B1508 thru B1520



B1508S thru B1524S



B1532S thru B1564S

| Part No. | Use With | | Thickness In. mm | Design Load Lbs. kN | Wt./C Lbs. kg |
|---------------|---------------|-------------------------|---------------------|------------------------|------------------|
| | EMT In. mm | Rigid Conduit In. mm | | | |
| B1508 | 1/2" (15) | – – | 16 Ga. (1.5) | 200 (.89) | 7.4 (3.4) |
| B1512 | 3/4" (20) | 1/2" (15) | 16 Ga. (1.5) | 200 (.89) | 8.0 (3.6) |
| B1516 | 1" (25) | 3/4" (20) | 14 Ga. (1.9) | 300 (1.33) | 11.0 (5.0) |
| B1520 | 1 1/4" (32) | 1" (25) | 14 Ga. (1.9) | 300 (1.33) | 12.5 (5.7) |
| B1508S | 1/2" (15) | – – | 16 Ga. (1.5) | 200 (.89) | 8.6 (3.9) |
| B1512S | 3/4" (20) | 1/2" (15) | 16 Ga. (1.5) | 200 (.89) | 9.2 (4.2) |
| B1516S | 1" (25) | 3/4" (20) | 14 Ga. (1.9) | 300 (1.33) | 12.7 (5.8) |
| B1520S | 1 1/4" (32) | 1" (25) | 14 Ga. (1.9) | 300 (1.33) | 14.6 (6.6) |
| B1524S | 1 1/2" (40) | 1 1/4" (32) | 12 Ga. (2.6) | 400 (1.78) | 20.5 (9.3) |
| B1532S | 2" (50) | 1 1/2" (40) | 12 Ga. (2.6) | 400 (1.78) | 21.5 (9.8) |
| B1534S | – – | 2" (50) | 12 Ga. (2.6) | 400 (1.78) | 22.7 (10.3) |
| B1540S | 2 1/2" (65) | 2 1/2" (65) | 12 Ga. (2.6) | 400 (1.78) | 26.0 (11.9) |
| B1548S | 3" (80) | 3" (80) | 12 Ga. (2.6) | 400 (1.78) | 30.2 (13.7) |
| B1556S | 3 1/2" (90) | 3 1/2" (90) | 12 Ga. (2.6) | 400 (1.78) | 33.3 (15.1) |
| B1564S | 4" (100) | 4" (100) | 12 Ga. (2.6) | 400 (1.78) | 36.6 (16.6) |

Reference page 168 for general fitting and standard finish specifications.