


## B22TH TH Type Channel

- For beam loads use 90% of Channel Loading Chart


Part No.	Thickness	Height H		Weight	
		In.	mm	Lbs./Ft.	kg/m
B22TH	12 Ga.(2.6)	1 <sup>5</sup> / <sub>8</sub> "	(41.3)	1.76	(2.62)



## B11KO6 thru B56KO6 KO6 Type Knockout Channel

- For beam loads use 90% of Channel Loading Chart


Part No.	Thickness	Height H		Weight	
		In.	mm	Lbs./Ft.	kg/m
B11KO6	12 Ga. (2.6)	3 <sup>1</sup> / <sub>4</sub> "	(82.5)	3.05	(4.54)
B12KO6	12 Ga.(2.6)	2 <sup>7</sup> / <sub>16</sub> "	(61.9)	2.47	(3.67)
B22KO6	12 Ga.(2.6)	1 <sup>5</sup> / <sub>8</sub> "	(41.3)	1.90	(2.83)
B24KO6	14 Ga.(1.9)	1 <sup>5</sup> / <sub>8</sub> "	(41.3)	1.40	(2.08)
B32KO6	12 Ga.(2.6)	1 <sup>3</sup> / <sub>8</sub> "	(34.9)	1.70	(2.53)
B42KO6	12 Ga.(2.6)	1"	(25.4)	1.44	(2.14)
B52KO6	12 Ga.(2.6)	1 <sup>3</sup> / <sub>16</sub> "	(20.6)	1.27	(1.89)
B54KO6	14 Ga.(1.9)	1 <sup>3</sup> / <sub>16</sub> "	(20.6)	.97	(1.44)



## B22SHA Back to Back SH Type Channel

- For beam loads use 90% of Channel Loading Chart

Part No.	Thickness	Height H		Weight	
		In.	mm	Lbs./Ft.	kg/m
B22SHA	12 Ga.(2.6)	3 <sup>1</sup> / <sub>4</sub> "	(82.5)	3.64	(5.42)
B52SHA	12 Ga.(2.6)	1 <sup>5</sup> / <sub>8</sub> "	(41.3)	2.38	(1.77)
B54SHA	14 Ga.(1.9)	1 <sup>5</sup> / <sub>8</sub> "	(41.3)	1.82	(1.35)



Reference page 48 for general fitting and standard finish specifications.