

A D V A N T A G E

Clampable Sway Brace Attachment

Features

- Maximum load of 975 Lbs. (includes safety factor of 5) when oriented across or along the beam.
- Torque all setscrews until head breaks off. (Speeds inspections and insures proper torque.)
- Attach brace at centerline of flange width.
- Available in zinc plated (ZN).
- Provides connection to structural steel (wide flange I beams) where drilling and/or welding is not permitted.

Part Number	Max. Flange Thickness	Flange Width
B800-1 x 4	3/4"	4"
B800-1 x 6	3/4"	6"
B800-1 x 8	3/4"	8"
B800-1 x 10	3/4"	10"
B800-1 x 12	3/4"	12"
B800-1 x 14	3/4"	14"
B800-1 x 16	3/4"	16"
B800-1 x 18	3/4"	18"
B800-2 x 4	1 1/4"	4"
B800-2 x 6	1 1/4"	6"
B800-2 x 8	1 1/4"	8"
B800-2 x 10	1 1/4"	10"
B800-2 x 12	1 1/4"	12"
B800-2 x 14	1 1/4"	14"
B800-2 x 16	1 1/4"	16"
B800-2 x 18	1 1/4"	18"

*Contact B-Line Engineering for OSHPD approval assistance.

509 West Monroe Street
Highland, Illinois 62249
Phone: 800-851-7415
Fax: 618-654-1917

Visit our website www.cooperbline.com for further information.

