



Fiberglass

BFP42 thru BFV42SH


- Channel lengths: 10 Ft. (3.05 m) and 20 Ft. (6.09 m)
- Fiberglass strut meets specification of ASTM D-4385 Levels III and IV.



**BFP42
BFV42
Solid Back**




**BFP42H1^{7/8}
BFV42H1^{7/8}
9/16" (14.3) holes
1 7/8" (47.6) on centers**



**BFP42SH
BFV42SH
9/16" (14.3) x 7/8" (22.2) slots
2" (50.8) on centers**


Part No.	Material	Description	Color	Weight Lbs./ft. kg/m
BFP42*	Polyester Resin	Solid Back	Gray	.48 (.71)
BFV42*	Vinyl Ester Resin	Solid Back	Beige	.48 (.71)
BFP42H1^{7/8}*	Polyester Resin	Holes in Back	Gray	.46 (.68)
BFV42H1^{7/8}*	Vinyl Ester Resin	Holes in Back	Beige	.46 (.68)
BFP42SH*	Polyester Resin	Slots in Back	Gray	.47 (.70)
BFV42SH*	Vinyl Ester Resin	Slots in Back	Beige	.47 (.70)




* Insert -10 for 10'-0" (3.05 m) length or -20 for 20'-0" (6.09 m) length

BFP42A BFV42A

- Channel lengths: 10 Ft. (3.05 m) and 20 Ft. (6.09 m)
- Fiberglass strut meets specification of ASTM D-4385 Levels III and IV.



**BFP42A
BFV42A
Solid Back to Back**



Part No.	Material	Description	Color	Weight Lbs./ft. kg/m
BFP42A*	Polyester Resin	Back To Back	Gray	.85 (1.26)
BFV42A*	Vinyl Ester Resin	Back To Back	Beige	.85 (1.26)

* Insert -10 for 10'-0" (3.05 m) length or -20 for 20'-0" (6.09 m) length

Published design loads on page 229 are based on usage at 70°F (21°C) and must be reduced for continuous exposure to higher temperatures. Refer to the chart below for high temperature applications.

Field Cutting Sealant Kits

RSK010

- Pint Sealing Kit (473 cm³) includes sealant and brush applicator
- Seals exposed fibers after field cutting
- UV resistant



APPROPRIATE PROTECTIVE CLOTHING AND RESPIRATORY PROTECTION DEVICE SHOULD BE WORN WHEN FIELD CUTTING OR GRINDING FIBERGLASS.

Temperature	Design Load Multiplier
75°F (24°C)	100%
100°F (38°C)	90%
125°F (52°C)	78%
150°F (66°C)	68%
175°F (79°C)	60%
200°F (93°C)	52%

Reference page 224 for general fitting specifications.