



## B811-\*

- \*Specify Width:  $W = 8, 12, 16$
- Can be attached directly to B809 & B812
- Standard finishes: ZN, HDG



## B812-\*


- \*Specify Depth:  $D = 6, 8, 12, 16, 18, 24$
- $13/16$ " (20.6mm) x 1" (25.4mm) banding slots for steel band
- Standard finishes: ZN, HDG



## B809B-\*

- \*Specify Depth:  $D = 6, 8, 10, 12, 16, 18, 24$
- $13/16$ " (20.6mm) x 1" (25.4mm) banding slots for steel band
- Standard finishes: ZN, HDG

Part No.	D		H	
	In.	mm	In.	mm
<b>B809B-6</b>	6"	(152.4)	12 <sup>3</sup> / <sub>4</sub> "	(323.9)
<b>B809B-8</b>	8"	(203.2)	14 <sup>3</sup> / <sub>4</sub> "	(374.7)
<b>B809B-10</b>	10"	(254.0)	16 <sup>3</sup> / <sub>4</sub> "	(425.5)
<b>B809B-12</b>	12"	(304.8)	18 <sup>3</sup> / <sub>4</sub> "	(476.2)
<b>B809B-16</b>	16"	(406.4)	22 <sup>3</sup> / <sub>4</sub> "	(577.8)
<b>B809B-18</b>	18"	(457.2)	24 <sup>3</sup> / <sub>4</sub> "	(628.6)
<b>B809B-24</b>	24"	(609.6)	27 <sup>3</sup> / <sub>4</sub> "	(704.8)



Reference page 106 for general fitting and standard finish specifications.