

Crescent® Brand Automotive And Chain Wrenches

CAUTION

1. Always wear approved eye protection.
2. Pipe wrenches should not be used to free “frozen” nuts or to final tighten nuts. Do not pull on a loosely adjusted wrench.
Never use a hammer or handle extension.
3. When possible, always pull rather than push on a pipe wrench and maintain proper stance on firm footing.

4. Never use a pipe wrench to bend, raise, or lift.
5. Use only box opening of combination wrenches, box wrenches or ratchet wrenches, to free “frozen” nuts or for final tightening of hex nuts. Never use a hammer or handle extension.
6. Use hex wrenches only to free “frozen” hex socket fasteners or for final tightening of same. Never use a hammer or handle extension.


Automotive Wrenches



- General purpose adjustable wrench
- Sliding jaw
- Forged from Crescent® special analysis tool steel
- Chrome-plated
- Precision machined; exceeds government specifications

Cat No.	UPC No.	Packed	Length		A		Pack wt.		Shelf Pack
			Inch	mm	Inch	mm	oz	g	
C79H	043127133183	Carded	9	229	2 3/4	70	4.56	2068	5
C711H	043127135163	Carded	11	279	3	76	7.75	3515	5
C715	043127213021	Boxed	15	381	3 5/8	92	3.25	1475	1
C718	043127067914	Boxed	18	457	4 3/8	111	4.25	1928	1

Chain Wrenches and Repair Chain



Concave-cut teeth for improved gripping. Easily resharpened if needed. U.S. Patent No. 3304817.



- Double-action allows use in either direction
- Designed for work in confined areas when ordinary pipe wrenches will not fit; excellent for pipe fittings
- Concave-cut teeth for improved gripping; easily resharpened if needed; U.S. Patent No. 3304817
- Chrome plated to resist rust
- Strong I-beam handle construction

Cat No.	UPC No.	Packed	Length		Capacity		Chain Length		Pack Wt.		Shelf Pack
			Inch	mm	Inch	mm	Inch	mm	lb	g	
CW12H	043127143175	Carded	12	305	4	102	15	375	9.38	4255	5
CW15	043127212925	Boxed	15	381	5	127	19	475	2.38	1080	1
CW24	043127212956	Boxed	24	610	6	152	23	575	3.56	1615	1

Replacement Chain for CW12, CW12H, CW15 and CW24 Wrenches

CW12C	043127067853	Boxed	12	305	4	102	15	375	0.79	358	1
CW15C	043127860966	Boxed	15	381	5	127	19	475	0.90	408	1
CW24C	043127860973	Boxed	24	610	6	152	23	575	1.10	499	1