


Current Transformer Metering

20 Amp, CT Meter Socket - 600 VAC



SW02132S1GR1N



Application

- Single meter position
- Designed for watt hour meters that meet ANSI C12.10
- Overhead or underground feed
- Surface mount

Construction

- Ringless cover
- Type 3R construction
- 16 Ga. galvaneal/galvanized steel

Standards

- UL 414 listed
- Complies with ANSI C12.7

Finish

- ANSI 61 gray painted finish

Accessories

- Replacement sockets
- AW hub assemblies
- Test switch bypass horn kit
- Lug kits
- Closing plates
- Touch-up paint



SW02132C2GR1T




Current Transformers

Part/UPC Number	Catalog Number	Service	Top Provision	Service Type	No. of Terminals	Bypass	Conductors Line/Load	Ground Prov. (Qty)	Overall Dimensions			Knockout Layout
									Height	Width	Depth	
20 Amp Continuous, CT Meter Socket with Pre-Wired Test Switch, 1 Piece Enclosure Cover												
78205138496	SW02062S1GR1N	UG	None	1Ø/3W	6	7 Pole TS without cover	#10-32 Stud	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 1
78205138495	SW02132S1GR1N	UG	None	3Ø/4W	13	10 Pole TS without cover	#10-32 Stud	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 1
20 Amp Continuous, CT Meter Socket with Pre-Wired Test Switch, 2 Piece Enclosure Cover												
78205158198	SW02062C2GR1T	UG	None	1Ø/3W	6	7 Pole TS with cover	#10-32 Stud	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 2
78205158197	SW02082C2GR1T	UG	None	3Ø/3W	8	7 Pole TS with cover	#10-32 Stud	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 2
78205138511	SW02132C2GR1T	UG	None	3Ø/4W	13	10 Pole TS with cover	#10-32 Stud	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 2
20 Amp Continuous, CT Meter Socket with Test Switch Provision, 2 Piece Enclosure Cover												
78205138512	SPO2133N2GRST	OH/UG	AWCAP	3Ø/4W	13	TS Provision	#14-#6	(2) #10-#2 AWG	20 ¹ / ₈ "	12 ¹ / ₄ "	5 ¹ / ₄ "	Fig. 3

TS = Test Switch

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.

Knockout Layouts



Knockouts - Conduit Sizes

- 1W = 1/4" dia.
- 1Z = 7/16" dia. (Barrel Lock KO)
- 2A = 1/2" - 3/8" dia.
- 5E = 1 1/2" - 1 1/4" - 1" - 3/4" - 1/2"
- HAW = AW Hub Opening (Small)

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.