


PHE3 66 16.7S SN7705 (769 714)



| Type | PHE3 66 16.7S SN7705 |
|---|---|
| Part No. | 769 714 |
| Nominal voltage (U _N) | 66 kV |
| Type of voltage | a.c. |
| Frequency | 16.7 Hz |
| Category | S |
| Total length (l _G) | 2980 mm |
| Insertion depth (l ₀) | 880 mm |
| Standard | EN/IEC 61243-1 (DIN VDE 0682-411) |
| Temperature range | -25 °C ... +55 °C, climatic category N |
| Design | Complete |
| For use at | Outdoor installations |
| For | Outdoor installations |
| Application | Overhead contact lines of electric railways |
| Design | Single-pole |
| Indication | Acoustic and visual |
| Self-testing element | Yes |
| Material (test electrode) | Copper alloy/gal Sn |
| Material (test prod) | Glass-fibre reinforced epoxy resin tube |
| Material (indicator) | Plastic, fully insulated |
| Material (insulating stick) | Glass-fibre reinforced polyester tube |
| Weight | 2,8 kg |
| Customs tariff number (Comb. Nomenclature EU) | 90303370 |
| GTIN | 4013364246768 |
| PU | 1 pc(s) |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.