

## HISC 1600 (785 310)



Figure without obligation

For dry and combined cleaning kits.

### Equipment:

25 l special plastic container, 2 large wheels, 2 swivel castors with brakes, handle and cable holder, device socket with automatic switch-on, electromagnetic pulse filter cleaning, automatic vibrator, speed controller, volume flow display, soft start control, electronic running feature, water detection with sensor-controlled disconnection, 2 new polyester filter cassettes, FKP 4300, filter area  $2 \times 4300 \text{ cm}^2 = 8600 \text{ cm}^2$ , dust collection capacity 99.99%, dust class L as per DIN EN 60335-2-69 Annex AA, cord length 8 m.

### Technical data:

Intake hose with straight connector  $\text{Ø}35 \text{ mm}$ , 5 m long

Type	HISC 1600
Part No.	785 310
Max. power	1600 W
Nominal voltage ( $U_N$ )	230 V
Max. air flow	75 l/s
Max. low air pressure	280 mbar
Container capacity	25 l gross volume, 20 l dust, 15 l water
Dimensions	450 x 390 x 490 mm
Weight	12,7 kg
Customs tariff number (Comb. Nomenclature EU)	85081900
GTIN	4013364092013
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.