

MOUNTING BRACKETS cont'd

Wall Bracket - Siding or Flat Wall

These hurricane rated wall brackets are strong, easy to install and are designed to be mounted into framing studs at 12" or 16" on center. These fit most mini-split models on the market today and provides the required distance between the wall and the condenser for optimal air flow. The QSWB2000 is rated for 300 lbs and the heavy duty QSWB4000 is rated for 600 lbs. Both models are also available in 316 stainless steel.



QSWB2000
QUICK-SLING
by DiversiTech



| CATALOG NO. | DESCRIPTION | UOM | ORDER MULTIPLE |
|-------------------|---|-----|----------------|
| QSWB2000 | Wall Bracket w/Z Bend | EA | 1 |
| QSWB2000SS | Wall Bracket w/Z Bend, Stainless Steel | EA | 1 |
| QSWB2000-3 | Wall Bracket w/Z Bend, 3 Mounting Arms | EA | 1 |
| QSWB2004 | Wall Bracket - Extra Large | EA | 1 |
| QSWB2005 | Wall Bracket - Extra Large, 3 Mounting Arms | EA | 1 |
| QSWB4000 | Wall Bracket w/Z Bend | EA | 1 |
| QSWB4000SS | Wall Bracket w/Z Bend, Stainless Steel | EA | 1 |

Pitched Roof Mini-Split Mounting Bracket

The Quick-Sling® Pitched Roof Mini-Split Mounting Bracket is a fast and easy solution to mounting outdoor condensing units to a sloped roof.




QSPR1000
QUICK-SLING
by DiversiTech

| CATALOG NO. | DESCRIPTION | UOM | ORDER MULTIPLE |
|-----------------|--|-----|----------------|
| QSPR1000 | Pitched Roof Bracket 300 lbs capacity, 9° - 45° sloped roofs | EA | 1 |

Air Conditioner Brackets

These heavy duty 10ga thick steel AC brackets are perfect for hanging A/C condensers and heat pumps outside the home. Mount at any height to allow for easy maintenance under units. No need to wait for finished grade or landscaping prior to installation of AC unit. Pre punched holes for easy installation. Powder coated gray finish. Load rating 600 lbs. per pair.



ACB-30



| CATALOG NO. | DESCRIPTION | UOM | ORDER MULTIPLE |
|------------------|--|-----|----------------|
| ACB-30 | AC Mounting Bracket - 30", pack of 2 | PK | 1 |
| ACB-36 | AC Mounting Bracket - 36", pack of 2 | PK | 1 |
| ACB-42 | AC Mounting Bracket - 42", pack of 2 | PK | 1 |
| ACB-48 | AC Mounting Bracket - 48", pack of 2 | PK | 1 |
| ACB-30-AL | AC Mounting Bracket, Aluminum - 30", pack of 2 | PK | 1 |
| ACB-36-AL | AC Mounting Bracket, Aluminum - 36", pack of 2 | PK | 1 |
| ACB-42-AL | AC Mounting Bracket, Aluminum - 42", pack of 2 | PK | 1 |
| ACB-48-AL | AC Mounting Bracket, Aluminum - 48", pack of 2 | PK | 1 |

Ductless Cassette Hangers

The Ductless Cassette Hangers are an innovative bracket design that is made of light-weight aluminum to provide quick and easy installation of ductless cassettes. Only two sku's are compatible with most of the ductless cassettes on the market today. The built-in adjustability allows the alignment of the unit after it has been hung.



QSCH1000



| CATALOG NO. | DESCRIPTION | UOM | ORDER MULTIPLE |
|-----------------|--|-----|----------------|
| QSCH1000 | Ductless Cassette Hanger - Small Holds up to 200 lbs. | EA | 1 |
| QSCH2000 | Ductless Cassette Hanger - Large Holds up to 200 lbs. | EA | 1 |

MINI-SPLIT STANDS

Mini-Split Stands

Our Quick-Sling® Mini-Split Stands provide a safe, stable platform to mount your unit on. It keeps unit elevated above lawn mowers, weed whackers, pets, snow, and flooding. The elevated height allows for ease of installation, maintenance and service. **Now available in Stainless Steel.**

| CATALOG NO. | DESCRIPTION | UOM | ORDER MULTIPLE |
|--------------------|---|-----|----------------|
| QSMS1200 | Mini-Split Stand Thin - 12" | EA | 1 |
| QSMS1201 | Mini-Split Stand Wide - 12" | EA | 1 |
| QSMS1201-SS | Mini-Split Stand Wide - 12" Stainless Steel | EA | 1 |
| QSMS1800 | Mini-Split Stand Thin - 18" | EA | 1 |
| QSMS1801 | Mini-Split Stand Wide - 18" | EA | 1 |
| QSMS1801-SS | Mini-Split Stand Wide - 18" Stainless Steel | EA | 1 |
| QSMS2400 | Mini-Split Stand Thin - 24" | EA | 1 |
| QSMS2401 | Mini-Split Stand Wide - 24" | EA | 1 |
| QSMS2401-SS | Mini-Split Stand Wide - 24" Stainless Steel | EA | 1 |



QSMS1201

