



Powering Business Worldwide

pe.eaton.com

Enclosed NEMA Lighting Contactor

84-29237-48

UPC:782114356265

Dimensions:

- **Height:** 11.688 IN
- **Length:** 7.313 IN
- **Width:** 7 IN

Weight:7 LB

Notes: Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Two-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eaton Specification Sheet - 84-29237-48](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data

