

## Eaton CPX9000 Clean power drive

**CPX02514EAP1**

**UPC:**782116941735

**Dimensions:**

- **Height:** 90 IN
- **Length:** 28.05 IN
- **Width:** 21.5 IN

**Weight:**800 LB

**Notes:**Brake chopper is standard in drives up to 30hp or 40hp at 480V, it is optional in larger drives. Some options are voltage and/or hp specific, consult your Eaton rep for details.

**Warranties:**

- 2 year

**Specifications:**

- **Input:** Input Disconnect
- **Application:** IH/internal brake chopper
- **Enclosure:** 7
- **Frame Size:** FR6
- **Horsepower:** 25 hp
- **Style:** Enclosed drive
- **Type:** Type 1
- **Voltage Rating:** 480 V

**Supporting documents:**

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [CPX9000 clean power drives in MCCs - the best solution for clean power](#)
- [Eaton Specification Sheet - CPX02514EAP1](#)

**Certifications:**

- UL 508C

**Product compliance:** No Data

