



Prepackaged kits containing a range of sizes are available.

Note: Because E-Z LOK inserts install with standard tools, our kits contain only inserts. Drills and taps are not included.

CARBON STEEL THREAD INSERTS FOR METAL

Kit Type	Kit Number	Quantity of Inserts	Insert Part Number	Internal Thread	External Thread
Coarse Thread #10 to 7/16"	EZ C107	10	329-3	10-24	3/8-16
		10	329-4	1/4-20	7/16-14
		10	329-5	5/16-18	1/2-13
		10	329-6	3/8-16	9/16-12
		8	329-7	7/16-14	5/8-11
Coarse Thread #10 to 1/2"	EZ C108	10	329-3	10-24	3/8-16
		10	329-4	1/4-20	7/16-14
		10	329-5	5/16-18	1/2-13
		10	329-6	3/8-16	9/16-12
		6	329-8	1/2-13	3/4-10
Coarse Thread 1/2" to 1"	EZ C816	6	329-8	1/2-13	3/4-10
		7	329-10	5/8-11	7/8-9
		7	329-12	3/4-10	1-8
		2	329-16	1-8	1-3/8-12
Fine Thread #10 to 7/16"	EZ F107	10	329-332	10-32	3/8-16
		10	329-428	1/4-28	7/16-14
		10	329-524	5/16-24	1/2-13
		10	329-624	3/8-24	9/16-12
		8	329-720	7/16-20	5/8-11
Fine Thread #10 to 1/2"	EZ F108	10	329-332	10-32	3/8-16
		10	329-428	1/4-28	7/16-14
		10	329-524	5/16-24	1/2-13
		10	329-624	3/8-24	9/16-12
		6	329-820	1/2-20	3/4-10
Fine Thread 1/2" to 1"	EZ F816	6	329-820	1/2-20	3/4-10
		7	329-10F	5/8-18	7/8-9
		7	329-1216	3/4-16	1-8
		2	329-1614	1-14	1-3/8-12

CARBON STEEL THREAD INSERTS FOR METAL — METRIC

Kit Type	Kit Number	Quantity of Inserts	Insert Part Number	Internal Thread	External Thread
M3-0.5 to M8-1.25	EZ M100	10	450-3	M3-0.5	M6-1.0
		10	450-4	M4-0.7	M8-1.25
		10	450-5	M5-0.8	M8-1.25
		10	450-6	M6-1.0	M10-1.5
		10	450-8	M8-1.25	M12-1.75
M8-1.25 to M16-2.0	EZ M200	10	450-8	M8-1.25	M12-1.75
		10	450-10	M10-1.5	M16-2.0
		8	450-12	M12-1.75	M16-2.0
		5	450-16	M16-2.0	M24-3.0
		10	550-3	10-24	M10-1.5
Coarse Thread #10 to 1/2"	EZ M508	10	550-4	1/4-20	M12-1.75
		10	550-5	5/16-18	M12-1.75
		10	550-6	3/8-16	M16-2.0
		6	550-8	1/2-13	M16-2.0
		10	650-6	M6-1.0	3/8-16
Metric Thread M6 to M12	EZ M612	10	650-8	M8-1.25	1/2-13
		10	650-10	M10-1.5	9/16-12
		6	650-12	M12-1.75	3/4-10

STAINLESS STEEL THREAD INSERTS FOR METAL

Kit Type	Kit Number	Quantity of Inserts	Insert Part Number	Internal Thread	External Thread
Coarse Thread 303 Stainless #10 to 1/2"	EZ C303	10	303-3	10-24	3/8-16
		10	303-4	1/4-20	7/16-14
		10	303-5	5/16-18	1/2-13
		10	303-6	3/8-16	9/16-12
		6	303-8	1/2-13	3/4-10
Fine Thread 303 Stainless #10 to 1/2"	EZ F303	10	303-332	10-32	3/8-16
		10	303-428	1/4-28	7/16-14
		10	303-524	5/16-24	1/2-13
		10	303-624	3/8-24	9/16-12
		6	303-820	1/2-20	3/4-10
M3-0.5 to M8-1.25	EZ M103	10	453-3	M3-0.5	M6-1.0
		10	453-4	M4-0.7	M8-1.25
		10	453-5	M5-0.8	M8-1.25
		10	453-6	M6-1.0	M10-1.5
		10	453-8	M8-1.25	M12-1.75
M8-1.25 to M16-2.0	EZ M203	10	453-8	M8-1.25	M12-1.75
		10	453-10	M10-1.5	M16-2.0
		8	453-12	M12-1.75	M16-2.0
		5	453-16	M16-2.0	M24-3.0
		10	653-6	M6-1.0	3/8-16
Metric Thread M6 to M12	EZ M613	10	653-8	M8-1.25	1/2-13
		10	653-10	M10-1.5	9/16-12
		10	653-12	M12-1.75	3/4-10
		6	653-12	M12-1.75	3/4-10



CARBON STEEL THREAD INSERTS FOR METAL — SINGLE PART NUMBER KITS

Kit Part No.	Insert Part No.	Internal Thread	External Thread	Insert Qty	Drill Size	Tap Size	Drive Tool
EZ-319-3	319-3	10-24	5/16-18	20	I	5/16-18	500-2
EZ-319-4	319-4	1/4-20	3/8-16	20	Q	3/8-16	500-3
EZ-319-5	319-5	5/16-18	7/16-14	20	X	7/16-14	500-4
EZ-319-6	319-6	3/8-16	1/2-13	20	29/64	1/2-13	500-5
EZ-319-7	319-7	7/16-14	9/16-12	20	33/64	9/16-12	500-6
EZ-319-8	319-8	1/2-13	5/8-11	20	37/64	5/8-11	500-7
EZ-319-332	319-332	10-32	5/16-18	20	I	5/16-18	500-2
EZ-319-428	319-428	1/4-20	3/8-16	20	Q	3/8-16	500-3
EZ-319-524	319-524	5/16-24	7/16-14	20	X	7/16-14	500-4
EZ-319-624	319-624	3/8-24	1/2-13	20	29/64	1/2-13	500-5
EZ-319-720	319-720	7/16-20	9/16-12	20	33/64	9/16-12	500-6
EZ-319-820	319-820	1/2-20	5/8-11	20	37/64	5/8-11	500-7