



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CN35 or A202 Enclosed Lighting Contactor

84-29237-9

UPC:782114341988

### Dimensions:

- **Height:** 11.688 IN
- **Length:** 7.313 IN
- **Width:** 7 IN

**Weight:**7 LB

**Notes:** Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Five-pole
- **Type:** Non-combination electrically held

### Supporting documents:

- [Eaton Specification Sheet - 84-29237-9](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data

