



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E59-M18C116C02-D3PP

UPC:786685105444

Dimensions:

- **Height:** .71 IN
- **Length:** 2.54 IN
- **Width:** .71 IN

Weight:.5 LB

Warranties:

- 1 year

Specifications:

- **Type:** E59
- **Accuracy:** <3% sensing range
- **Contact Rating:** 300 mA at 6-48 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 1NO-1NC
complementary output
- **Cord Length:** 79.2 FT
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12,
13, IP67, IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Dc Current:** 300 mA
- **Operating Mode:** Unshielded
- **Operating Temperature:** -40° to 158°F (-40° to
70°C)
- **Protection:** Auto reset
- **Temperature Rating:** -40° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [iProx sensors](#)
- [Eaton Specification Sheet - E59-M18C116C02-D3PP](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.