

## Eaton C30CN mechanically held lighting contactor

ECC03C1A2A-C18

UPC:786685233574

### Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

**Weight:**13 LB

**Notes:**Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 110 V/50 Hz, 120 V/60 Hz
- **Contact Rating:** 30 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Two-pole
- **Operation:** Electrically held
- **Series:** C30CN Series
- **Special Features:** 2 NC power pole
- **Type:** Non-combination electrically and mechanically held

### Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECC03C1A2A-C18](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data



