

## Eaton C30CN mechanically held lighting contactor

ECC03C1H8A-P8P23

UPC:782116155101

### Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

**Weight:**13 LB

**Notes:**Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Accessories:** ON/OFF pushbutton, red RUN pilot light
- **Amperage Rating:** 30A
- **Coil Voltage:** 277V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Eight-pole
- **Type:** Non-combination electrically held

### Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECC03C1H8A-P8P23](#)

### Certifications:

- cUL Listed
- UL Listed

**Product compliance:** No Data



