



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## C30CN Enclosed Lighting Contactor

ECC04C1A2A-P7

UPC:782116155682

### Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

**Weight:**13 LB

**Notes:**Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Accessories:** START/STOP pushbutton
- **Amperage Rating:** 30A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Two-pole
- **Type:** Non-combination mechanically held and magnetically latched

### Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECC04C1A2A-P7](#)

### Certifications:

- cUL Listed
- UL Listed

**Product compliance:** No Data



