

Eaton CN35 electrically held lighting contactor

ECL03B1B1A

UPC:782116139460

Dimensions:

- **Height:** 12.6 IN
- **Length:** 7.73 IN
- **Width:** 5.84 IN

Weight:5.2 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 220V/50 Hz, 240V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Single-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL03B1B1A](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

