

## Eaton CN35 electrically held lighting contactor

ECL03B1C6A

UPC:782116139545

### Dimensions:

- **Height:** 12.6 IN
- **Length:** 7.73 IN
- **Width:** 5.84 IN

**Weight:**5.2 LB

**Notes:**Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 440 V/50 Hz, 480 V/60 Hz
- **Contact Rating:** 20 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Ten-pole
- **Operation:** Electrically held
- **Series:** A202 Series
- **Type:** Non-combination electrically held

### Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL03B1C6A](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data



