



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL03E1T3A

UPC:782114274330

Dimensions:

- **Height:** 28.313 IN
- **Length:** 13.188 IN
- **Width:** 11.563 IN

Weight:41 LB

Notes: Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 100A
- **Coil Voltage:** 24V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 90 mm
- **Number Of Poles:** Three-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL03E1T3A](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data

