

## Eaton A202 magnetically held lighting contactor

**ECL04C1A4A-A29**

**UPC:**782114192450

**Dimensions:**

- **Height:** 13.21 IN
- **Length:** 7.73 IN
- **Width:** 5.84 IN

**Weight:**12.5 LB

**Notes:**When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

**Warranties:**

- 1 year

**Specifications:**

- **Amperage Rating:** 30A
- **Auxiliary Contact:** Side-mounted
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Contact Configuration:** 1NO-1NC
- **Contact Rating:** 30 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Four-pole
- **Series:** A202 Series
- **Type:** Non-combination mechanically held and magnetically latched

**Supporting documents:**

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL04C1A4A-A29](#)



**Certifications:**

- cUL Listed
- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.