

Eaton A202 magnetically held lighting contactor

ECL04C1B2A

UPC:782114041581

Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

Weight:13 LB

Notes:When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 220V/50 Hz, 240V/60 Hz
- **Contact Rating:** 30 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Two-pole
- **Operation:** MECH held and MAG latched
- **Series:** A202 Series
- **Type:** Non-combination mechanically held and magnetically latched

Supporting documents:

- [Lighting contactors](#)
- [Eaton's Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL04C1B2A](#)

Certifications:



- UL Listed
- cUL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.