

Eaton A202 magnetically held lighting contactor

ECL04D1A3A-S3

UPC:786685358369

Dimensions:

- **Height:** 13.21 IN
- **Length:** 7.73 IN
- **Width:** 5.84 IN

Weight:12.7 LB

Notes:When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Accessories:** HAND/OFF/AUTO selector switch
- **Amperage Rating:** 60A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Contact Rating:** 60 A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Three-pole
- **Operation:** MECH held and MAG latched
- **Series:** A202 Series
- **Special Features:** Two-wire control relay
- **Type:** Non-combination mechanically held and magnetically latched

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL04D1A3A-S3](#)



Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.