

CN35 or A202 Enclosed Lighting Contactor

ECL12F1C3J

UPC:782114019368

Dimensions:

- **Height:** 38.375 IN
- **Length:** 30.75 IN
- **Width:** 12.375 IN

Weight:152 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Coil Voltage:** 440V/50 Hz, 480V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Type:** Combination electrically held lighting fusible disconnect
- **Amperage Rating:** 200A
- **Frame Size:** 180 mm
- **Fuse Clip Rating:** 200A/600V
- **Number Of Poles:** Three-pole

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL12F1C3J](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

