

Irrigation Pump Panel

ECP5532CAG-R63/E

UPC:786685455938

Dimensions:

- **Height:** 10 IN
- **Length:** 32 IN
- **Width:** 15.5 IN

Weight:67 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 460V/60 Hz, 440V/50 Hz
- **Enclosure:** NEMA 3R
- **Circuit Breaker Rating:** 100A
- **Disconnect:** Circuit breaker
- **Frame Size:** NEMA size 3
- **Overload Relay:** 20-100A solid-state overload relay

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Irrigation pump panel](#)
- [Eaton Specification Sheet - ECP5532CAG-R63/E](#)

Certifications:

- UL Listed
- OSHPD Certified
- cUL Listed
- ABS Certified

Product compliance: No Data
