

CN35 or A202 Enclosed Lighting Contactor

ECL14D4A3F

UPC:782114272107

Dimensions:

- **Height:** 30.125 IN
- **Length:** 11.625 IN
- **Width:** 10.25 IN

Weight:38 LB

Notes:When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Stainless steel
- **Type:** Combination electrically held thermal magnetic circuit breaker
- **Amperage Rating:** 60A
- **Frame Size:** 65 mm
- **Fuse Clip Rating:** 100A/250V
- **Number Of Poles:** Three-pole

Supporting documents:

- [Lighting contactors](#)
- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECL14D4A3F](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.