



Powering Business Worldwide

pe.eaton.com

Mini-Power Center

P60G11S10H

UPC:786680051838

Dimensions:

- **Height:** 32.5 IN
- **Length:** 11.6 IN
- **Width:** 13.1 IN

Weight:240 LB

Notes:HFD type primary breaker

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Mini-power center
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3R
- **Frame:** 285
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 600V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 10 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 108B10K

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P60G11S10H](#)

Certifications:

- IEEE Certified
- UL Listed



- ANSI

Product compliance:

- NEMA Compliant

© 2016 Eaton. All rights reserved.