

PRODUCT: | **E6010**

PURPOSE: | **BENCH TOP FIXED-SPEED RECIPROCAL SHAKER**

Eberbach's Bench top Fixed-Speed Reciprocal Shakers are designed for your lab's general purpose shaking needs. If your sample preparations do not require a variable speed shaker the two speed E6010 is the choice for dependability and longevity. This heavy-duty shaker power unit operates in a space of 16.5" x 11" and utilizes Eberbach's rocker arm suspension system. Model E6010 is a two-speed unit, operating at either 180 or 280 osc/min (+/- 5%) and controlled by a three position switch. The E6010 has a horizontal stroke fixed at 1.5", and a maximum load capacity of 40 lbs. Many options and accessories are available for this model, please contact Eberbach for more details.



E6010 with E6040 Box Carrier



Stainless Steel Model With optional Dual Carrier and Stand

PRODUCT SPECIFICATIONS...

OPERATING SPEED:	Fixed speed 180 - 280 osc/min
STROKE:	1.5" Horizontal Fixed
TYPE OF MOUNTING:	<ul style="list-style-type: none"> • Bench top • Suction cup feet to prevent creeping
LOAD CAPACITY:	Accepts up to 40 lbs
POWER REQUIREMENTS:	115V 60Hz or 230V, 50/60Hz, 3 wire UL listed power cord
SIZE AND WEIGHT:	Length: 16.5", Width: 11", Height: 10" (without box carrier or stand) Weight: 56 lbs
OPTIONS:	<p>Setup Options</p> <ul style="list-style-type: none"> • Flask holders (E6090) of various sizes can be mounted on platform (E6061) • Utility box carrier with anti-slide surface and one (1) rubber coated crossbar is available to hold various beakers, flasks, bottles, etc. (E6040) • Platform tiering bars available for doubling unit's shaking capacity (E6190/91) • Variable speed with digital tach and timer, Order No. E6013.00 • Stainless Steel Wash-Down models available

Built with Rocker Arm Technology - See Page 34 for details.

DURABILITY • CRAFTSMANSHIP • QUALITY

1-800-422-2558 | WWW.EBERBACHLABTOOLS.COM